PRELIMINARY DATASHEET

LUVOCOM® 3F PAHT CF 9891 BK



High-temperature polyamide with carbon fibers, black

Disconing I was a setting		T 4 4l	C	11	Touris alonation
Physical properties		Test method	Specimen	Units	Typical value
Specific gravity		ISO 1183-3		g/cm³	1,24
Water absorption	23°C / 24h	ISO 62	MPTS ISO 3167 A	%	<0,3
Melt flow rates (MFR)	250°C / 2,16kg	ISO 1133	pellet	g/10 min	3,4
Melt volume rate (MVR)	250°C / 2,16kg	ISO 1133	pellet	cm ³ /10 min	3,0
Linear mould shrinkage		DIN 16742	MPTS ISO 3167 A	%	0,3-0,5
Mechanical properties at 23°C / 5	0% rh				
Tensile strength	dry, @50 mm/min	ISO 527	MPTS ISO 3167 A	MPa	130
Elongation at maximum force	dry, @50 mm/min	ISO 527	MPTS ISO 3167 A	%	2
Modulus of elasticity	dry, @1 mm/min	ISO 527	MPTS ISO 3167 A	GPa	11,5
Charpy impact strength	dry	ISO 179 1eU	80x10x4mm	kJ/m²	35
Thermal properties					
Heat distortion temperature	HDTA	ISO 75	molded sample	°C	90
Continuous service temperature	20.000 h	IEC 60216	MPTS ISO 3167 A	°C	120
Service temperature	during lifetime max. 200h		MPTS ISO 3167 A	°C	160
Electrical properties					
Insulation resistance strip electrode	R25	DIN IEC 60167	MPTS ISO 3167 A	Ω	≤10²
Surface resistance	ROB	DIN IEC 60093	Ronde 60x4mm	Ω	<10²

Main features

Low influence from moisture and temperature to measures and electrical properties, compared with PA66



LUVOCOM® 3F PAHT CF 9891 BK



High-temperature polyamide with carbon fibers, black

Recommended processing parameters

General

3D Printing parameters may vary from machine to machine. The following settings may be used as an indication: nozzle temperature: $265 - 290 \,^{\circ}\text{C}$ / nozzle material: abbrasion resistant / print bed temperature: $> 50 \,^{\circ}\text{C}$ / layer thickness: $> 0.2 \,^{\circ}\text{mm}$ / printing speed $40 - 60 \,^{\circ}\text{mm}$ /s.

The processing notes provided merely represent a recommendation for general use. Due to the large variety of machines, geometries and volumes of parts, etc., it may be necessary to employ different settings according to the specific application. Please contact us for further information.

Predrying

It is advisable to predry the granulate with a suitable dryer immediately before processing. The granulate may absorb moisture from the environment.

Dryer type	Temperature °C	Drying time in h	
Dehumidifying dryer	130	6 - 8	
Vacuum Dryer	120	4 - 6	
Processing			
Zone 1	°C	260 - 300	
Zone 2	°C	260 - 300	
Zone 3	°C	260 - 300	
Nozzle	°C	250 - 290	
Melt temperature	°C	280	

In general LUVOCOM® 3F can be processed on conventional extrusion machines while observing the usual technical guidelines. Any added fibrous materials or fillers may have an abrasive effect. In this case the cylinder, screw and die should be protected against wear as is usual in the processing of reinforced thermoplastic materials. Lengthy dwell times for the melts in the cylinder should be avoided. Lower the temperatures during interruptions!

Delivery form & storage

Unless indicated otherwise, the material is delivered as 3mm long pellets in sealed bags on pallets. Preferably storage should be effected in dry and normally temperatured rooms.

Additional information

Filaments produced from this material may be wound into standard size spools.

09891 21 06 18

Europe and Head Office

Lehmann&Voss&Co. KG Alsterufer 19 20354 Hamburg Germany Tel +49 40 44 197-530 Email: luvocom@lehvoss.de

North America

LEHVOSS North America, LLC 185 South Broad Street Pawcatuck, CT 06379 USA Tel +1-855-681-3226

Email: info@lehvoss.us

Asia

LEHVOSS (Shanghai) Chemical Trading Co., Ltd. Unit 4805, 8 Xingyi Road Changning District, Shanghai 200336 China Tel +86 21 62785181 Email: info@lehvoss.cn



